

PMC SI6A061Z/EC 1x 5A

8C000011



Technical data at 3 x 400 V AC: Nominal output current: 1x 5 A @ 4kHz / 1x 4.5 A @ 8kHz. I_{max}: 210% for 2s / 250% for 2s. Apparent power: 3.5 KVA. Without brake resistor. Option: Without Safety module technology, with EtherCat.

Tekniske data

Generelle data	
Godkendelse:	UL Listed, CE, UKCA
Teknisk data	
Elektriske data	
Forsyningsspænding 2 (V):	24 - 24 V
Forsyningsspændingstype U2:	DC
Indgange	
Miljøoplysninger	
Omgivelsestemperatur:	0 - 45 °C
Køletype:	indbygget ventilator
Mekaniske data	
Mål, højde:	343 mm
Mål, bredde:	45 mm
Mål, dybde:	265 mm
Nettovægt:	3030 g
Bruttovægt:	4650 g
Miljø	
WEEE klassifikation (08/2018):	5 devices (feed size < 50cm)
Kommercielle data	
Harmonized System Code:	85044085

UNSPSC 25:	39121007
EAN-kode:	4046548100174
ECLASS Version:	ECLASS-13
ECLASS Reference Feature:	27023101
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000017
ETIM Reference Feature:	EC001857
Volumen:	0

Nødvendigt driftstilbehør



8C000006

PMC SI6A061 terminal set (Y/Z)