

Brake resistor 600W/33R/T/U

8176372

suitable for the PMCprotego D/01-12A and PM Ctendo DD4/01-20A Type: FZECQU 400 x 65-33 Performance at 40? C/100 % ED: 600 W Resistance value: 33 OHM Temperature switch 180? C: Signal contact 2A/24 V DC (DC11) UL version.



Tekniske data

Generelle data	
Godkendelse:	CE
Teknisk data	
Mekaniske data	
Nettovægt:	3000 g
Bruttovægt:	3500 g
Miljø	
RoHS-overensstemmelse:	ja
Overholdelse af REACH:	Indeholder ingen SVHC-stoffer
WEEE klassifikation (08/2018):	0 not relevant
Kommercielle data	
Harmonized System Code:	85333900
UNSPSC 25:	39121021
EAN-kode:	4046548059250
ECLASS Version:	ECLASS-13
ECLASS Reference Feature:	27023291
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000017
ETIM Reference Feature:	EC002025
Volumen:	0