

## PMC SI6A161Y/EC 1x 12A

8C000025



Technical data at 3 x 400 V AC: Nominal output current: 1x 12 A @ 4kHz / 1x 10 A @ 8kHz. I<sub>max</sub>: 210% for 2s / 250% for 2s. Apparent power: 8.3 KVA. Without brake resistor. Option: Safety module SY6 (STO and SS1 using FSoE) and EtherCat.

## Tekniske data

| Generelle data                 |                              |
|--------------------------------|------------------------------|
| Godkendelse:                   | UL Listed, CE, UKCA          |
| Teknisk data                   |                              |
| Elektriske data                |                              |
| Forsyningsspænding 2 (V):      | 24 - 24 V                    |
| Forsyningsspændingstype U2:    | DC                           |
| Indgange                       |                              |
| Miljøoplysninger               |                              |
| Omgivelsestemperatur:          | 0 - 45 °C                    |
| Køletype:                      | indbygget ventilator         |
| Mekaniske data                 |                              |
| Mål, højde:                    | 343 mm                       |
| Mål, bredde:                   | 65 mm                        |
| Mål, dybde:                    | 286 mm                       |
| Nettovægt:                     | 3930 g                       |
| Bruttovægt:                    | 5310 g                       |
| Miljø                          |                              |
| WEEE klassifikation (08/2018): | 5 devices (feed size < 50cm) |
| Kommercielle data              |                              |
| Harmonized System Code:        | 85044085                     |

|                           |               |
|---------------------------|---------------|
| UNSPSC 25:                | 39121007      |
| EAN-kode:                 | 4046548100457 |
| ECLASS Version:           | ECLASS-13     |
| ECLASS Reference Feature: | 27023101      |
| ETIM Version:             | ETIM-9.0      |
| ETIM Reference Group:     | EG000017      |
| ETIM Reference Feature:   | EC001857      |
| Volumen:                  | 0             |

## Nødvendigt driftstilbehør



8C000022

PMC SI6A161 Terminal set (Y/Z)