

## Modular gateway PROFINET IRT

Article No.: 100074



### Technical Data

|                                         |                                                                             |
|-----------------------------------------|-----------------------------------------------------------------------------|
| Housing dimensions (H x W x D)          | 96 x 22,5 x 110,5 mm                                                        |
| Housing type                            | DIN rail housing (for DIN rail version EN 50022)                            |
| Housing material                        | Polycarbonate                                                               |
| Weight                                  | approx. 90 g                                                                |
| Protection class                        | IP20                                                                        |
| Power supply                            | 24 V DC -20 %/+25 %                                                         |
| Max. power consumption                  | max. 100 mA during operation                                                |
| Operating temperature                   | 0 to +60 °C                                                                 |
| Storage temperature                     | -25 to +60°C                                                                |
| Humidity (40°C)                         | up to 93% (non-condensing)                                                  |
| Optical indicator                       | Five status LEDs                                                            |
| Configuration                           | PROFINET                                                                    |
| Fieldbus connection                     | 2x RJ45                                                                     |
| Device type                             | Slave                                                                       |
| Fieldbus interface                      | PROFINET                                                                    |
| Protokoll                               | IRT                                                                         |
| Maximum data length Input data          | 512 Byte                                                                    |
| Maximum data length Ouput data          | 512 Byte                                                                    |
| Compatible modules for system expansion | RevPi base modules and modular gateways can be connected by using a bridge. |
| Conformance                             | RoHS                                                                        |
| Qualification                           | CE                                                                          |
| Certification                           | Approved by the PROFINET user organization (PNO)                            |