




|                                      |          |          |                       |            |           |                                                             |                |              |
|--------------------------------------|----------|----------|-----------------------|------------|-----------|-------------------------------------------------------------|----------------|--------------|
| Refer to protection notice ISO 18016 | -        | 20210167 | 23.08.2021            | PD-SUP-MD  | PD-SUP-MD | Neue Zeichnung<br>new Drawing                               |                |              |
|                                      | Index    | ECO no.  | Date                  | Editor     | Checked   |                                                             |                |              |
|                                      | Scale    | 1:1      |                       |            | Date      | Name                                                        | MODEL: 2031314 | DRW: 2031315 |
|                                      | Material |          | Created               | 23.08.2021 | PD-SUP-MD | Internet Dokument<br>Internet document<br>MotEZ_301_UDAPC50 |                |              |
|                                      |          |          | Checked               | 23.08.2021 | PD-SUP-MD |                                                             |                |              |
|                                      |          |          | Norm                  | -          | -         |                                                             |                |              |
|                                      | Surface  |          | Unspecified tolerance |            |           | Doc.-No.                                                    | 2031315        | Page 1       |
|                                      |          |          | ISO 2768 - mH         |            |           | Mat.-No.                                                    | 8G000001       | of 1         |