










Ø46	g6	45.991 - 45.975
Ø20	g7	19.993 - 19.972
20	H7	20.021 - 20
5	JS9	5.015 - 4.985
Ø4	m6	4.012 - 4.004
4	K7	4.003 - 3.991
dimensions	fit	tolerance of dim.

Obscene protection note to DIN 34	-	20120576	19.07.2013	EP-MK	EP-MK	-			
	Index	ECC no.	Date	Editor	Checked	-			
	Scale	1:1			Date	Name	MODEL: 2013393	DRW: 2013394	
	Material			Created	19.7.2013	EP-MK	Internet Dokument Internet document PSEN enc S1 eCAM		
	-			Checked	19.7.2013	EP-MK			
	-			Norm	-	-			
			All dimensions are in mm						
	Surface		Unspecified tolerance				Doc.-No.	2013394	Page 1
	-						Mat.-No.	-	of 1
	-								
-									