









3	N9	2.996 - 2.971
Ø10	h7	10 - 9.985
Ø50	h7	50 - 49.975
dimensions	fit	tolerance of dim.

Observe protection made to DIN 34	-	20120576	19.07.2013	EP-MK	EP-MK	-			
	Index	ECO no.	Date	Editor	Checked	-			
	Scale			Date	Name	MODEL: 2013395	DRW: 2013396		
	1:1		Created	19.7.2013	EP-MK	Internet Dokument Internet document PSEN enc S2 eCAM			
	Material		Checked	19.7.2013	EP-MK				
	-	Norm	-	-					
	-	All dimensions are in mm							
	Surface	Unspecified tolerance					Doc.-No.	2013396	Page 1
	-						Mat.-No.	-	of 1

