

PSEN sl-1.0 VA 1actuator

570650



Actuator (free-moving), coded, for safety locking device PSENslock, stainless steel base plate (1.4301), for holding force 1000 N

Technical details

General data	
Approval:	CE, UKCA, cULus Listed, FCC, IC, TÜV, EAC (Eurasian)
Sensor principle:	Transponder
Coding level to ISO 14119:	Low
Transponder coding:	coded
unit type:	Actuator
Technical data	
Environmental data	
Ambient temperature standard:	EN 60068-2-14
Ambient temperature:	-25, 55
Storage temperature standard:	EN 60068-2-1/-2
Climatic suitability standard:	EN 60068-2-78
Humidity rating:	93 % r. h. at 40 °C
EMC to standard ...:	EN 55011: Class A, EN 60947-5-3, EN 62061
Vibration to standard ...:	EN 60947-5-2
Acc. shock to standard1:	30g
Mechanical data	
Housing material upper part:	PBT
Material of anchor plate:	Nickel-plated steel
Material actuator:	Stainless steel 1.4301

Height dimension:	188
Width dimension:	52
Depth dimension:	22
Net weight:	1080
Gross weight:	1160
Environment	
WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
Harmonized System Code:	85389099
UNSPSC 25:	39122205
EAN-Code:	4046548064261
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27272606
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000026
ETIM Reference Feature:	EC001487
Volume:	0

Optional accessories



540312

PSEN screw M5x20 10pcs



570550

PSEN sl bracket swing door



570551

PSEN sl bracket sliding door