

PIT si 1.2 muting lamp self monitoring

620020



PITsign muting lamp in accordance with EN 61496 including incandescent lamp and wall mounting, permanent light with option for monitoring, UB = 24 V DC/ 7 W / 500 mA, 2 semiconductor outputs for function monitoring, protection type housing: IP65, diameter: 100 mm, height: 138.5 mm, signal lamp for Muting operation.

Technical details

General data

Approval:	CE, UKCA, cULus Listed, TÜV
Self-monitored:	ja
Lamp:	Glühbirne
Lamp type:	BA15d, 24 V DC, 7W
Elec. service life signal lamp:	1.000 Stunden

Technical data

Electrical data

Supply voltage (V):	24, 24
Type of supply voltage U1:	DC
Power consumption DC:	7

Semiconductor outputs

Number of semicond. outputs:	2
S/C output short circuit proof:	ja

Environmental data

Ambient temperature:	0, 50
EMC to standard ...:	EN 61000-6-2

Mechanical data

Cable entry:	ISO 20 mm
Mounting position:	upright

Housing material of cover:	PC
Housing material lower section:	ABS
Connection terminal:	Screw terminal
Height dimension:	138.5
Diameter:	100
Net weight:	218
Gross weight:	351
Environment	
WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
Harmonized System Code:	85311095
UNSPSC 25:	39121534
EAN-Code:	4046548002607
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27143209
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000035
ETIM Reference Feature:	EC001332
Volume:	2.657