

PSEN ml 1.1 round actuator

570482

Actuator with rounded head, coded, for safety guard locking device PSENmlock,



Technical details

General data

Approval:	CE, UKCA, cULus Listed, TÜV
Sensor principle:	Transponder
Coding level to ISO 14119:	Low
Transponder coding:	coded
unit type:	Actuator

Technical data

Environmental data

Ambient temperature standard:	EN 60068-2-14
Ambient temperature:	0, 60
Storage temperature standard:	EN 60068-2-1/-2
Climatic suitability standard:	EN 60068-2-78
Humidity rating:	93 % r. h. at 40 °C
EMC to standard ...:	EN 55011: Class A, EN 60947-5-3, EN 61326-3-1
Vibration to standard ...:	EN 60947-5-2
Acc. shock to standard1:	50g
UL enclosure type:	Type 1

Mechanical data

Max. vertical offset:	+/-3.0 mm
Max. ang. offset round X axis:	+/-2.0 deg

Max. ang. offset round Y axis:	+/-2.5 deg
Max. ang. offset round Z axis:	+/-7.5 deg
Max. offset closing direction:	+/-2 mm
Product material:	Zn, Galvanised steel, Plastic, Stainless steel, Polycarbonate
Net weight:	145
Gross weight:	190
Environment	
WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
Harmonized System Code:	85389099
UNSPSC 25:	39122205
EAN-Code:	4046548094954
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27272606
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000026
ETIM Reference Feature:	EC001487
Volume:	0