

PSEN cs1.19-OSSD2 1actuator

540383



RFiD actuator for safety switch PSEN cs1.19, IP67, PU = 1 piece, OSSD2.

Technical details

General data	
Approval:	CE, UKCA, cULus Listed, TÜV, EAC (Eurasian)
Sensor principle:	Transponder
Transponder coding:	coded
unit type:	Actuator
Technical data	
Environmental data	
Ambient temperature standard:	EN 60068-2-14
Ambient temperature:	-25, 55
Storage temperature standard:	EN 60068-2-1/-2
Climatic suitability standard:	EN 60068-2-78
Humidity rating:	93 % r. h. at 40 °C
EMC to standard ...:	EN 60947-5-3
Vibration to standard ...:	EN 60947-5-2
Acc. shock to standard1:	30g
Overvoltage category:	III
Pollution degree clear.&creep.:	3
Mechanical data	
Housing material upper part:	PBT
Height dimension:	11

Width dimension:	40
Depth dimension:	40
Net weight:	20
Gross weight:	25
Transponder	
Operating frequency:	122 kHz - 128 kHz
Environment	
RoHS directive:	2011/65/EU, 2015/863/EU
RoHS conformity:	yes
RoHS exceptions:	no
REACH compliance:	Contains no SVHC substances
WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
Harmonized System Code:	85389099
UNSPSC 25:	39122205
EAN-Code:	4046548070743
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27274002
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000026
ETIM Reference Feature:	EC001487
Volume:	0

Optional accessories



540311

PSEN screw M5x10 10pcs



540312

PSEN screw M5x20 10pcs
