

PDP67 F 4 code

773603



Decentralised passive distributor for connection of PSENcode, PSENslock and PSENini to a Pilz control system, max. 4 sensors, protection type IP67.

Technical details

General data	
Approval:	CE, UKCA, cULus Listed, KOSHA
Technical data	
Electrical data	
Supply voltage (V):	24 - 24 V
Type of supply voltage U1:	DC
Environmental data	
Climatic suitability to ...:	EN 60068-2-2, EN 60068-2-1, EN 60068-2-14
Ambient temperature standard:	EN 60068-2-14
Ambient temperature:	-40 - -40 °C
Storage temperature standard:	EN 60068-2-1/-2
Climatic suitability standard:	EN 60068-2-78
Humidity rating:	93 % r. h. at 40 °C
Condensation permitted?:	Briefly
Vibration to standard ...:	EN 60068-2-6
Clearance & creepage dist. to:	EN 60664-1
Overvoltage category:	II
Pollution degree clear.&creep.:	2
Mechanical data	
Housing material upper part:	PBT

Connection terminal:	M12
Terminal style:	screw interlocked
Height dimension:	120 mm
Width dimension:	60 mm
Depth dimension:	20 mm
Net weight:	240 g
Gross weight:	295 g
Environment	
REACH compliance:	contains min. 1 SVHC-substance
WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
Harmonized System Code:	85389091
UNSPSC 25:	39122214
EAN-Code:	4046548063011
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27440108
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000026
ETIM Reference Feature:	EC002585
Volume:	0.354

Obligatory accessories



773610

PDP67 Connector cs

Optional accessories



540342

PSEN cable M12-8sf M12-8sm, 10m



540343

PSEN cable M12-8sf M12-8sm, 20m



540344

PSEN cable M12-8sf M12-8sm, 30m



540340

PSEN cable M12-8sf M12-8sm, 2m



540341

PSEN cable M12-8sf M12-8sm, 5m