

PMC PS6A34 50A/20KW

8C000003



Supply module for PMC SI6 drive controller. Technical data at 3 x 400 V AC: Nominal input current: 50 A. Maximum input current: 180% for 5s / 150% for 30s. Nominal power 20kW

Technical details

General data	
Approval:	UL Listed, CE, UKCA
Technical data	
Electrical data	
Supply voltage with phases:	3×400 VAC, +32/−50 %, 50/60 Hz, 3×480 VAC, +10/−58 %, 50/60 Hz
Supply voltage 2 (V):	24 - 24 V
Type of supply voltage U2:	DC
Environmental data	
Ambient temperature:	0 - 45 °C
Cooling type:	Built-in fan
Mechanical data	
Height dimension:	343 mm
Width dimension:	65 mm
Depth dimension:	219 mm
Net weight:	3820 g
Gross weight:	4920 g
Environment	
WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
Harmonized System Code:	85044085

UNSPSC 25:	39121007
EAN-Code:	4046548100129
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27023101
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000017
ETIM Reference Feature:	EC001857
Volume:	0

Obligatory accessories



8C000004

PMC PS6A34 terminal set