

PIT oe 4S

402311



Pushbutton unit with 4 LED pushbuttons, including fixing nuts. Optional accessories for PIT m4 SEU [402250].

Technical details

General data	
Approval:	CE, UKCA,
Technical data	
Electrical data	
Supply voltage (V):	24, 24
Type of supply voltage U1:	DC
Power consumption DC:	0.17
Inputs	
Signal level at input at 0:	< 5 V
Environmental data	
Climatic suitability to ...:	EN 60068-2-2, EN 60068-2-1, EN 60068-2-14
Ambient temperature standard:	EN 60068-2-2, EN 60068-2-1
Ambient temperature:	-20, 60
Storage temperature standard:	EN 60068-2-1/-2
Climatic suitability standard:	EN 60068-2-78
Humidity rating:	93 % r. h. at 40 °C
Perm. operating height ASL:	2000 m
EMC to standard ...:	EN 61131-2 (Zone B)
Vibration to standard ...:	EN 60068-2-6
Acc. shock to standard1:	150 m/s ²

Clearance & creepage dist. to:	EN 61131-2
Overvoltage category:	II
Pollution degree clear.&creep.:	2
Protection type standard:	EN 60529
Mechanical data	
Mounting position:	any
Connection terminal:	Spring-loaded terminal
Height dimension:	32
Width dimension:	32
Depth dimension:	40
Net weight:	17
Gross weight:	25
Environment	
WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
Harmonized System Code:	85365011
UNSPSC 25:	39122205
EAN-Code:	4046548097962
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27379213
ETIM Version:	ETIM-9.0
Volume:	0