

PIT js2

401100



PITjog manually operated control device 3 built-in pushbuttons, connection via 10-pin coiled cable with open end.

Technical details

General data

Approval:	CE
Self-monitored:	nein

Technical data

Electrical data

Supply voltage (V):	24, 24
Type of supply voltage U1:	AC/DC

Push button

Number, pushbutton:	3
---------------------	---

Relay outputs

Voltage DC1 safety cont.:	24
---------------------------	----

Environmental data

Ambient temperature:	-10, 55
----------------------	---------

Mechanical data

Length cable:	5
Material of cable insulation 1:	PUR
Conductor cross section:	0.14
Housing material:	PC-ABS-Blend UL 94V0
Height dimension:	341
Width dimension:	75

Depth dimension:	60
Net weight:	837
Gross weight:	951
Environment	
RoHS directive:	2011/65/EU, 2015/863/EU
RoHS conformity:	yes
RoHS exceptions:	yes
RoHS except.s acc. to direct.:	6c
REACH compliance:	contains min. 1 SVHC-substance
REACH included substances:	Lead
%-part of the pollutant:	> 0,1
CAS No.:	7439-92-1
WEEE classification (08/2018):	5 devices (feed size < 50cm)
SCIP entry available:	yes
Commercial data	
Harmonized System Code:	85365011
UNSPSC 25:	32131023
EAN-Code:	4046548024463
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27371244
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000017
ETIM Reference Feature:	EC002034
Volume:	0