

PSEN cs5.1 1actuator

542080

RFiD actuator for safety switch PSEN cs5.x, IP67, PU = 1 piece.



Technical details

General data

Approval:	CE, UKCA, cULus Listed, TÜV, ECOLAB, EAC (Eurasian)
Sensor principle:	Transponder
Coding level to ISO 14119:	Low
Transponder coding:	coded
unit type:	Actuator

Technical data


Environmental data

Ambient temperature standard:	EN 60068-2-14
Ambient temperature:	-25, 70
Max. ambient temp. at Hmax:	+60 °C
Max. ambient temp. at 2000 m:	+70 °C
Storage temperature standard:	EN 60068-2-1/-2
Climatic suitability standard:	EN 60068-2-30
Humidity rating:	93 % r. h. at 40 °C
Perm. operating height ASL:	4000 m
EMC to standard ...:	EN 60947-5-3
Vibration to standard ...:	EN 60947-5-2
Acc. shock to standard1:	30g

Mechanical data

Housing material upper part:	PBT
Height dimension:	18
Width dimension:	37
Depth dimension:	13
Net weight:	10
Gross weight:	15
Transponder	
Operating frequency:	122 kHz - 128 kHz
Environment	
RoHS directive:	2011/65/EU, 2015/863/EU
RoHS conformity:	yes
RoHS exceptions:	no
REACH compliance:	Contains no SVHC substances
WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
Harmonized System Code:	85389099
UNSPSC 25:	39122205
EAN-Code:	4046548077346
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27274002
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000026
ETIM Reference Feature:	EC001487
Volume:	0

Optional accessories



540310

PSEN screw M4x16 10pcs

532111

PSEN mag/cs bracket straight



532110

PSEN Winkel / bracket



540309

PSEN screw M4x12 10pcs

