

PSEN me3 / 2AS

570210



Mechanical safety switch, with standard actuator, contacts: 1 N/O, 1 N/C.

Technical details

General data

Approval:	CE, cCSAus, TÜV, EAC (Eurasian)
unit type:	Unit

Technical data

Relay outputs

Utilisation cat. AC/DC1 stand.:	EN 60947-4-1
Voltage AC1 safety cont.:	240 V
Max. current AC1 safety cont.:	10 A
Utilisation cat. AC15/DC13sta.:	EN 60947-5-1
Voltage AC15 safety cont.:	240 V
Max. current AC15 safety cont.:	3 A

Environmental data

Ambient temperature:	-30 - 80 °C
----------------------	-------------

Mechanical data

Connection terminal:	Screw terminal
Terminal style:	fixed
Height dimension:	90 mm
Width dimension:	52 mm
Depth dimension:	33 mm
Net weight:	151 g

Gross weight:	204 g
Environment	
RoHS directive:	2011/65/EU, 2015/863/EU
RoHS conformity:	yes
RoHS exceptions:	yes
RoHS except.s acc. to direct.:	6c
REACH compliance:	contains min. 1 SVHC-substance
REACH included substances:	Lead, ETU
%-part of the pollutant:	> 0,1
CAS No.:	7439-92-1, 96-45-7
WEEE classification (08/2018):	5 devices (feed size < 50cm)
SCIP entry available:	yes
Commercial data	
Harmonized System Code:	85365080
UNSPSC 25:	39122205
EAN-Code:	4046548002782
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27272603
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000026
ETIM Reference Feature:	EC002593
Volume:	0

Optional accessories



380706

PDP67 cable M12-5sm, 10m



380707

PDP67 cable M12-5sm, 20m



380705

PDP67 cable M12-5sm, 3m



380708

PDP67 cable M12-5sm, 30m



540312

PSEN screw M5x20 10pcs



773600

PDP67 F 8DI ION



570793

PSEN cable 200m-8x0.25mm²