

PSSnet SLL 4T 1FMMSC

380604



Industrial Ethernet Switch, unmanaged 4 x standard 10/100 BASE TX, RJ45 ports, 1 x 100BASE-FX Multimode SC port.

Technical details

General data

Approval: CE, UKCA, cULus Listed

Technical data

Electrical data

Supply voltage (V): 10 - 32 V

Type of supply voltage U1: DC

Environmental data

Ambient temperature: -40 - 70 °C

Humidity rating: 95 % r. h. at 40 °C

EMC to standard ...: EN 55022 Class A, EN 61000-4-4, FCC CFR47 Part 15 Class A, EN 61000-4-5, EN 61000-4-6, EN 61000-4-2, EN 61000-4-3

Vibration to standard ...: EN 60068-2-6

Acc. shock to standard1: 15g

Pollution degree clear.&creep.: 2

Mechanical data

Height dimension: 114 mm

Width dimension: 25 mm

Depth dimension: 79 mm

Net weight: 119 g

Gross weight: 224 g

Environment

WEEE klassifikation (08/2018):	6 small IT-/communic. device
Commercial data	
ECLASS version:	ECLASS-9.1
ECLASS Reference Feature:	19170106
ETIM Version:	ETIM-7.0
ETIM Reference Group:	EG000037
ETIM Reference Feature:	EC000734

Optional accessories



380000

SafetyNET p Cable per mtr



380400

SafetyNET p Connector RJ45s