

RevPi DIO

Z9000012



Digital expansion module DIO for the base module RevPi Core / RevPi Core 3, housing dimensions (H x W x D): 96 x 22.5 x 110.5 mm, protectiontype: IP 20, number of digital inputs: 14, number of digital outputs: 14, max. current per output: 500 mA (High-Side mode), 100 mA (Push-Pull mode).

Technical details

General data	
Approval:	CE, UKCA, cULus Listed
Technical data	
Mechanical data	
Height dimension:	96 mm
Width dimension:	22.5 mm
Depth dimension:	110.5 mm
Net weight:	102 g
Gross weight:	130 g
Environment	
WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
Harmonized System Code:	84714900
UNSPSC 25:	39122331
EAN-Code:	4046548093254
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27242290
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000024
ETIM Reference Feature:	EC001422

Volume:

0

Optional accessories



Z9000016

GW Connector for Modular Gateways