

PMC PS6A24 25A/10KW

8C000001



Supply module for PMC SI6 drive controller. Technical data at 3 x 400 V AC: Nominal input current: 25 A. Maximum input current: 180% for 5s / 150% for 30s. Nominal power 10kW

Technical details

General data

Approval: UL Listed, CE, UKCA

Technical data

Electrical data

Supply voltage with phases: 3×400 VAC, +32/−50 %, 50/60 Hz, 3×480 VAC, +10/−58 %, 50/60 Hz

Supply voltage 2 (V): 24 - 24 V

Type of supply voltage U2: DC

Environmental data

Ambient temperature: 0 - 45 °C

Cooling type: Built-in fan

Mechanical data

Height dimension: 343 mm

Width dimension: 45 mm

Depth dimension: 204 mm

Net weight: 2680 g

Gross weight: 4180 g

Environment

WEEE classification (08/2018): 5 devices (feed size < 50cm)

Commercial data

Harmonized System Code: 85044085

UNSPSC 25:	39121007
EAN-Code:	4046548100112
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27023101
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000017
ETIM Reference Feature:	EC001857
Volume:	0

Obligatory accessories



8C000002

PMC PS6A24 terminal set