

PSEN me5M NC.NC n 1 switch

6L000021



Mechanical safety gate system PSENmech, with M12 connection 5-pin, interlock principle magnetic force, contacts interlocking 1 N/C, contacts guard locking 1 N/C, supply voltage 24 V AC/DC.

Technical details

General data

Approval:	CSA, CE, CCC, UKCA, DGUV
Suitable for series connection:	yes
unit type:	Sensor

Technical data

Electrical data

Supply voltage (V):	24, 24
Type of supply voltage U1:	AC/DC

Relay outputs

Utilisation cat. AC15/DC13sta.:	EN 60947-5-1
Voltage DC13 safety cont.:	24

Environmental data

Ambient temperature:	-25, 55
Overvoltage category:	II

Mechanical data

Holding force:	1500
Connection type:	M12, 5-pin male
Height dimension:	192
Width dimension:	42
Depth dimension:	44

Net weight:	489
Gross weight:	541
Environment	
RoHS directive:	2011/65/EU, 2015/863/EU
RoHS conformity:	yes
RoHS exceptions:	yes
RoHS except.s acc. to direct.:	6C
REACH compliance:	contains min. 1 SVHC-substance
REACH included substances:	Lead
%-part of the pollutant:	> 0,1
CAS No.:	7439-92-1
WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
Harmonized System Code:	85365019
UNSPSC 25:	39122205
EAN-Code:	4046548101508
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27272603
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000026
ETIM Reference Feature:	EC002593
Volume:	1.258

Optional accessories



380209

PSS67 Cable M12sf M12sm, 5m



630347

PSEN op cable angle M12 5-pole 3m



540308

PSEN screw M4x10 10pcs



630348

PSEN op cable angle M12 5-pole 5m



630349

PSEN op cable angle M12 5-pole 10m



540309

PSEN screw M4x12 10pcs



630350

PSEN op cable angle M12 5-pole 30m



630298

PSEN cable M12-5sf 20m



380320

PSS67 I/O Cable



630310

PSEN op cable axial M12 5-pole 3m



630297

PSEN op cable axial M12 5-pole 30m



380220

PSS67 cable M12-5sf, M12-5sm, 20m



380208

PSS67 Cable M12sf M12sm, 3m



6L000006

PSEN me5 20mm extension



6L000007

PSEN me5 40mm extension



6L000008

PSEN me5 emergency release front



6L000009

PSEN me5 emergency release back



540310

PSEN screw M4x16 10pcs



540311

PSEN screw M5x10 10pcs



6L000005

PSEN me5 escape release



630311

PSEN op cable axial M12 5-pole 5m



630312

PSEN op cable axial M12 5-pole 10m



630364

PSEN op cable axial M12 5-pole 50m



380210

PSS67 Cable M12sf M12sm, 10m



630365

PSEN op cable angle M12 5-pole 50m



380211

PSS67 Cable M12sf M12sm, 30m



380214

PSS67 Cable M12af M12am, 10m



380710

PDP67 Cable M12-5sf M12-5sm, 0.5m



380215

PSS67 Cable M12af M12am, 30m



380212

PSS67 Cable M12af M12am, 3m



380213

PSS67 Cable M12af M12am, 5m



380713

PDP67 Cable M12-5sf M12-5sm, 2m



380711

PDP67 Cable M12-5sf M12-5sm, 1m



380712

PDP67 Cable M12-5sf M12-5sm, 1.5m