

PSEN hs1.2p

570271



Safe hinge switch, mounting position left-hand side, M12 4-pin maleconnector, 2 N/C, IP67.

Technical details

General data	
Approval:	CE, BG, cCSAus
Door hinge:	Left
Technical data	
Relay outputs	
Utilisation cat. AC15/DC13sta.:	EN 60947-5-1
Voltage AC15 safety cont.:	230 V
Max. current AC15 safety cont.:	3 A
Voltage DC13 safety cont.:	24 V
Environmental data	
Ambient temperature:	-25 - 70 °C
Mechanical data	
Connection type:	M12
Height dimension:	147 mm
Width dimension:	82 mm
Depth dimension:	19.5 mm
Net weight:	330 g
Gross weight:	376 g
Environment	
RoHS directive:	2011/65/EU, 2015/863/EU

RoHS conformity:	yes
RoHS exceptions:	no
REACH compliance:	Contains no SVHC substances
WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
Harmonized System Code:	85365080
UNSPSC 25:	39122205
EAN-Code:	4046548062410
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27272601
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000026
ETIM Reference Feature:	EC000030
Volume:	0

Optional accessories



630308

PSEN op cable angle M12 4-p. shield. 10m



630309

PSEN op cable axial M12 4-p. shield. 30m



630302

PSEN op cable axial M12 4-pole 10m



630303

PSEN op cable axial M12 4-p. shield. 3m



630366

PSEN op cable axial M12 4-p. shield. 50m



630344

PSEN op cable angle M12 4-pole 30m



630300

PSEN op cable axial M12 4-pole 3m



630367

PSEN op cable angle M12 4-p. shield. 50m



630301

PSEN op cable axial M12 4-pole 5m



630306

PSEN op cable angle M12 4-p. shield. 3m



630307

PSEN op cable angle M12 4-p. shield. 5m




540308

PSEN screw M4x10 10pcs



630304

PSEN op cable axial M12 4-p. shield. 5m



540309

PSEN screw M4x12 10pcs



630305

PSEN op cable axial M12 4-p. shield. 10m



630270

PSEN op cable axial M12 4-p. shield. 20m



380320

PSS67 I/O Cable




630296

PSEN op cable axial M12 4-pole 30m



630319

PSEN op cable angle M12 4-p. shield. 30m



540310

PSEN screw M4x16 10pcs



540311

PSEN screw M5x10 10pcs



630342

PSEN op cable angle M12 4-pole 5m



630343

PSEN op cable angle M12 4-pole 10m



630362

PSEN op cable axial M12 4-pole 50m



630363

PSEN op cable angle M12 4-pole 50m



630341

PSEN op cable angle M12 4-pole 3m