

PMC SC6A261R/EC 1x 19A

8C000079



Technical data at 3 x 400 V AC: Nominal output current: 1x 19 A @ 4kHz / 1x 15 A @ 8kHz. I_{max}: 210% for 2s / 250% for 2s. Apparent power: 13.2 KVA. Without brake resistor. Option: Safety module SR6 (STO using terminals) and EtherCat.

Technical details

General data

Approval: UL Listed, CE, UKCA

Technical data

Electrical data

Supply voltage with phases: 3×400 VAC, +32/−50 %, 50/60 Hz, 3×480 VAC, +10/−58 %, 50/60 Hz

Supply voltage 2 (V): 24 - 24 V

Type of supply voltage U2: DC

Inputs

Environmental data

Ambient temperature: 0 - 45 °C

Cooling type: Built-in fan

Mechanical data

Height dimension: 343 mm

Width dimension: 65 mm

Depth dimension: 286 mm

Net weight: 5250 g

Gross weight: 6450 g

Environment

WEEE classification (08/2018): 5 devices (feed size < 50cm)

Commercial data

Harmonized System Code:	85044085
UNSPSC 25:	39121007
EAN-Code:	4046548100587
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27023101
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000017
ETIM Reference Feature:	EC001857
Volume:	0

Obligatory accessories



8C000077

PMC SC6A261 terminal set (R)