

PIT oe 4S

402311



Pushbutton unit with 4 LED pushbuttons, including fixing nuts. Optional accessories for PIT m4 SEU [402250].

Technical details

General data

Approval: CE, UKCA,

Technical data

Electrical data

Supply voltage (V): 24, 24

Type of supply voltage U1: DC

Power consumption DC: 0.17

Inputs

Signal level at input at 0: < 5 V

Environmental data

Climatic suitability to ...: EN 60068-2-2, EN 60068-2-1, EN 60068-2-14

Ambient temperature standard: EN 60068-2-2, EN 60068-2-1

Ambient temperature: -20, 60

Storage temperature standard: EN 60068-2-1/-2

Climatic suitability standard: EN 60068-2-78

Humidity rating: 93 % r. h. at 40 °C

Perm. operating height ASL: 2000 m

EMC to standard ...: EN 61131-2 (Zone B)

Vibration to standard ...: EN 60068-2-6

Acc. shock to standard1: 150 m/s²

Clearance & creepage dist. to:	EN 61131-2
Overvoltage category:	II
Pollution degree clear.&creep.:	2
Protection type standard:	EN 60529
Mechanical data	
Mounting position:	any
Connection terminal:	Spring-loaded terminal
Height dimension:	32
Width dimension:	32
Depth dimension:	40
Net weight:	17
Gross weight:	25
Environment	
WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
Harmonized System Code:	85365011
UNSPSC 25:	39122205
EAN-Code:	4046548097962
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27379213
ETIM Version:	ETIM-9.0
Volume:	0