

PSEN cs4.1 Key gy2

541182



Transponder key for PSEN cs4.1p, grey "2" marking, material: plastic, accessories: key adapter (532113)

Technical details

General data

Approval:	CE, UKCA, cULus Listed, FCC, IC, TÜV, EAC (Eurasian)
Sensor principle:	Transponder
Coding level to ISO 14119:	High
Transponder coding:	fully coded
unit type:	Actuator

Technical data

Environmental data

Ambient temperature standard:	EN 60068-2-14
Ambient temperature:	-10, 55
Storage temperature standard:	EN 60068-2-1/-2
Climatic suitability standard:	EN 60068-2-78
Humidity rating:	93 % r. h. at 40 °C
EMC to standard ...:	EN 60947-5-3
Vibration to standard ...:	EN 60947-5-2
Acc. shock to standard1:	30g

Mechanical data

Housing material upper part:	PBT
Height dimension:	15.1
Width dimension:	42

Depth dimension:	8
Net weight:	5
Gross weight:	6
Transponder	
Operating frequency:	122 kHz - 128 kHz
Environment	
WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
Harmonized System Code:	85389099
UNSPSC 25:	39122205
EAN-Code:	4046548096675
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27274692
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000026
ETIM Reference Feature:	EC002997
Volume:	0