

RevPi AIO

Z9000015



Analogue expansion module AIO for the base module RevPi Core / RevPi Core 3, housing dimensions (H x W x D): 96 x 22.5 x 110.5 mm, protectiontype: IP 20, number of input channels: 6, number of output channels: 2, for current, voltage, RTDs, output voltage ranges: ± 10 V, ± 11 V, ± 5 V, ± 5.5 V, 0...10 V, 0...11 V, 0...5 V, 0...5.5 V, output current ranges: 0...20 mA, 0...24 mA, 4...20 mA.

Technical details

General data	
Approval:	CE, UKCA
Technical data	
Mechanical data	
Height dimension:	96 mm
Width dimension:	22.5 mm
Depth dimension:	110.5 mm
Net weight:	108 g
Gross weight:	136 g
Environment	
WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
Harmonized System Code:	84714900
UNSPSC 25:	39122331
EAN-Code:	4046548093117
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27242290
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000024
ETIM Reference Feature:	EC001422

Volume:

0

Optional accessories



Z9000016

GW Connector for Modular Gateways