

PSEN rsm 2.0-300-0-0-0

570306



Rope pull switch incl. E-STOP pushbutton, straight head, plastic housing, 2 NC and 2 NO contacts, 300 N max. spring force

Technical details

General data

Approval: CE, CCC, cULus Listed

Technical data

Relay outputs

Utilisation cat. AC15/DC13sta.: EN 60947-5-1

Voltage AC15 safety cont.: 240 V

Max. current AC15 safety cont.: 3 A

Voltage DC13 safety cont.: 250 V

Environmental data

Ambient temperature: -30 - 75 °C

Mechanical data

Housing material lower section: PA

Housing material upper part: PA

Material actuator: Zn die cast

Connection terminal: Screw terminal

Height dimension: 42.5 mm

Width dimension: 151 mm

Depth dimension: 67 mm

Net weight: 246 g

Gross weight: 314 g

Environment	
RoHS directive:	2011/65/EU, 2015/863/EU
RoHS conformity:	yes
RoHS exceptions:	no
REACH compliance:	Contains no SVHC substances
WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
Harmonized System Code:	85365080
UNSPSC 25:	39122205
EAN-Code:	4046548104912
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27270607
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000017
ETIM Reference Feature:	EC002033
Volume:	0

Optional accessories



570318

PSEN rsm rope thimble



570319

PSEN rsm rope clamp



570316

PSEN rsm turnbuckle



570317

PSEN rsm turnbuckle nut



570314

PSEN rs rope d3/d4 50m



570315

PSEN rs rope d3/d4 100m



570312

PSEN rs pulley 75



570313

PSEN rs pulley flex



570311

PSEN rs spring 300



570793

PSEN cable 200m-8x0.25mm²