

PMCable M2/B1B2/020/1Q5/S1

8177144



Power cable; Cable assembled on both sides Crimp connectors <> con.23 round connector 8-pin SpeedTec; No. of wires and cross section (4x1.5+1x (2 x 1.0)); suitable for PM Ctendo DD5 and the motors PM Ctendo SZ..4x...K to SZ.73...K; Length 20 m.

Technical details

Technical data	
Environmental data	
Ambient temperature:	-20 - 60 °C
Mechanical data	
Connector type 1:	8-pin M8 female connector
Shape of connector type 1:	straight
Connector type 2:	Crimp connector
Contact surfaces material 1:	Au
Contact surfaces material 2:	Sn
Length cable:	20 m
Material shield surface K1:	Sn
Colour cable insulation 1:	Orange
Material of cable insulation 1:	PUR
Trailing capability of cable 1:	yes
Max. outside diameter cable K1:	10.2 - 11 mm
Cross section data cable K1:	(4 x 1.50 + 2 x 1.0) mm ²
Shielding K1:	yes
Type of shielding K1:	Wire mesh
Net weight:	3600 g
Gross weight:	4200 g

Environment	
WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
Harmonized System Code:	85444290
UNSPSC 25:	26121603
EAN-Code:	4046548074345
ECLASS version:	ECLASS-13
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000026
ETIM Reference Feature:	EC001855