

PSSu K S RS232

312439



PSSu, compact module, standard, serial interface, RS232, 1 input, 2 communication channels, 64 Bit, full duplex mode, 7 transmission rates, configurable, 0.6 - 19.2 kBit/s, hardware handshake CTS/RTS, potential isolation, cable length 15 m.

Technical details

General data

Approval:	CE, UKCA, cULus Listed, TÜV
Application range:	Standard

Technical data

Serial interface


Number of RS 232 interfaces:	1
------------------------------	---

Environmental data

Climatic suitability to ...:	EN 60068-2-30, EN 60068-2-2, EN 60068-2-1, EN 60068-2-78, EN 60068-2-14
Ambient temperature standard:	EN 60068-2-14
Ambient temperature:	0 - 60 °C
Storage temperature standard:	EN 60068-2-1/-2
Climatic suitability standard:	EN 60068-2-30, EN 60068-2-78
Humidity rating:	93 % r. h. at 40 °C
Condensation permitted?:	Not permitted
Perm. operating height ASL:	2000 m
EMC to standard ...:	EN 61131-2, EN 61000-4-4, EN 61000-4-5, EN 61000-4-6, EN 61000-4-2, EN 61000-4-3
Vibration to standard ...:	EN 60068-2-6
Acc. shock to standard1:	15g
Clearance & creepage dist. to:	EN 61131-2, IEC 60664-1

Overvoltage category:	II
Pollution degree clear.&creep.:	2
Protection type standard:	EN 60529
Mechanical data	
Mounting position:	horizontal on top hat rail
Housing material lower section:	PC
Housing material front plate:	PC
Connection terminal:	D-sub male
Height dimension:	128.9 mm
Width dimension:	30 mm
Depth dimension:	56 mm
Net weight:	81 g
Gross weight:	86 g
Environment	
REACH compliance:	contains min. 1 SVHC-substance
WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
Harmonized System Code:	85389091
UNSPSC 25:	39122331
EAN-Code:	4046548073485
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27242605
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000024
ETIM Reference Feature:	EC001601
Volume:	0.358

Obligatory accessories



313116

PSSu A Con 3/30 C (2 pcs.)



313115

PSSu A Con 1/10 C (2 pcs.)

Optional accessories



312966

PSSu A LC 0.1 (5 pcs.)



312900

PSSu A ET (10 pcs.)



312902

PSSu A EC



312901

PSSu A ETM (2 pcs.)



312958

PSSu A LA0 (10 x 108 pcs.)



312949

PSSu A ET PE (10 pcs.)