

Cable Can PMCLink>PMCLink:L=0,7m

1803117



Cable assembled on both sides, Connector Sub-D9 male <> connector Sub-D9 female CAN network, length: 0.7 m.

Technical details

Technical data

Mechanical data

Shape of connector type 1:	straight
Shape of connector type 2:	straight
Length cable:	0.7 m
Colour cable insulation 1:	Grey
Trailing capability of cable 1:	no
Shielding K1:	yes
Type of shielding K1:	Wire mesh
Net weight:	140 g
Gross weight:	140 g

Environment

WEEE classification (08/2018):	5 devices (feed size < 50cm)
--------------------------------	------------------------------

Commercial data

Harmonized System Code:	85444290
UNSPSC 25:	26121603
EAN-Code:	4046548028256
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27242009
ETIM Version:	ETIM-9.0



THE SPIRIT OF SAFETY

ETIM Reference Group:	EG000024
ETIM Reference Feature:	EC002584
Volume:	0