

PNOZ e2.1p 24VDC 2so

774136



Safety relay (standalone), inputs: On the basis of the requirement class III C in accordance with EN 574, outputs: 2 safety outputs, 1 auxiliary output of SC type, UB = 24 V DC, width: 22.5 mm, plug-in terminals of screw type, automatic start, connection between several devices.

Technical details

General data

Approval: CE, UKCA, cULus Listed, EAC (Eurasian), TÜV

Technical data

Electrical data

Supply voltage (V): 24 - 24 V

Type of supply voltage U1: DC

Max. device circuit breaker: 6 A slow / 10 A quick

Type of two-hand device: III C

Semiconductor outputs

Utilisation cat. to EN 60947-1: DC-12

Environmental data

Climatic suitability to ...: EN 60068-2-78

Ambient temperature: -10 - -10 °C

Humidity rating: 93 % r. h. at 40 °C

Condensation permitted?: Not permitted

EMC to standard ...: EN 60947-5-1, EN 61000-6-2, EN 61000-6-4, EN 61326-3-1

Vibration to standard ...: EN 60068-2-6

Clearance & creepage dist. to: EN 60947-1

Overvoltage category: III

Pollution degree clear.&creep.: 2

Mechanical data	
Mounting position:	any
Housing material front plate:	ABS UL 94 V0
Connection terminal:	Screw terminal
Terminal style:	plug-in
Flex. cond. c/s AWG info:	24 - 12 AWG
Height dimension:	94 mm
Width dimension:	22.5 mm
Depth dimension:	121 mm
Net weight:	130 g
Gross weight:	145 g
Environment	
RoHS directive:	2011/65/EU, 2015/863/EU
RoHS conformity:	yes
RoHS exceptions:	yes
RoHS except.s acc. to direct.:	7a, 7c I
REACH compliance:	contains min. 1 SVHC-substance
REACH included substances:	Lead, Lead oxide
%-part of the pollutant:	> 0,1%
CAS No.:	7439-92-1, 1317-36-8
WEEE classification (08/2018):	5 devices (feed size < 50cm)
SCIP entry available:	yes
Commercial data	
Harmonized System Code:	85365019
UNSPSC 25:	39122205
EAN-Code:	4046548011944
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27371821
ETIM Version:	ETIM-9.0

ETIM Reference Group:	EG000019
ETIM Reference Feature:	EC001452
Volume:	0.285

Optional accessories



774195

Terminal block filter 1



774196

Terminal block filter 2



374280

PNOZ X Set plug in screw terminals P1+P2