

PSEN opII lockout

632510

Accessory reset lock for PSEN opII safety light curtain. PU = 1 lockout, 2 one-way screws M4x12, 1 threaded pin M3x12, 2 slot nuts.



Technical details

Technical data

Environmental data

Ambient temperature:	-30 - 60 °C
Vibration lockout closed:	Closed
Vibration to stand. CLOSED:	EN 60068-2-6
Vibration lockout open:	Open
Vibration to standard ...:	EN 60068-2-6
Vibration to standard 2:	EN 60068-2-6
Vibration to standard 3:	EN 60068-2-6
Accel. shock to stand. CLOSED:	2g
Bracket for shock standard 1:	Swivel mount
Acc. shock to standard1:	10g
Bracket for shock standard 2:	Adv Bracket Kit
Acc. shock to standard2:	25g
Shock class 2:	3M7
Bracket for shock standard 3:	Adv Bracket Kit
Bracket for shock standard 4:	Adv Bracket Kit
Accel. shock to standard4:	40g
Bracket for shock standard 5:	Swivel mount
Shock class 5:	3M4

Mechanical data	
Product material:	Aluminium, Coated steel
Torque+tolerance screws:	2.1 Nm +/-0.2 Nm
Tightening torque threaded pin:	0,4 Nm +/- 0,04 Nm
Height dimension:	66 mm
Width dimension:	55 mm
Depth dimension:	22 mm
Net weight:	195 g
Gross weight:	250 g
Environment	
WEEE classification (08/2018):	0 not relevant
Commercial data	
Harmonized System Code:	85389099
UNSPSC 25:	39121528
EAN-Code:	4046548096224
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27272792
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000026
ETIM Reference Feature:	EC003015
Volume:	0