

AFZ A 1 s

350001

Delay-on energisation timer for use on PLC systems 1 s, 1 semiconductor output PNP, LED for power indicator Housing for panel mounting 22.5 mm, protection type IP66.

Technical details

Technical data

Electrical data

Supply voltage (V): 24 - 24 V

Type of supply voltage U1: DC

Power consumption DC: 0.3 W

Relay outputs

Relay contact material: AgCdO

Environmental data

Climatic suitability to ...: DIN IEC 60068-2-3

Ambient temperature: -10 - 55 °C

Humidity rating: 93 % r. h. at 40 °C

Condensation permitted?: Not permitted

Clearance & creepage dist. to: VDE 0110-1

Mechanical data

Mounting position: any

Depth dimension: 34 mm

Net weight: 17 g

Gross weight: 17 g

Optional accessories



374007

H-REDUZIERRING
