

FB/F10/3SEC./POT.2,2MOHM

325205



Remote controller for timer, panel-mount housing for 22.5 mm, absolute scale, max. 10 s / 2.2 mOhm, time setting is via rotary knob, protection type IP66.

Technical details

General data	
Approval:	-
Technical data	
Environmental data	
Ambient temperature:	-10 - 55 °C
Condensation permitted?:	Not permitted
Mechanical data	
Mounting position:	any
Net weight:	20 g
Gross weight:	20 g
Environment	
WEEE classification (08/2018):	5
Commercial data	
Harmonized System Code:	85334010
UNSPSC 25:	39122331
EAN-Code:	4046548018059
ECLASS version:	ECLASS-9.1
ECLASS Reference Feature:	27379106
ETIM Version:	ETIM-7.0
ETIM Reference Group:	EG000019



THE SPIRIT OF SAFETY

ETIM Reference Feature:

EC002586