

RevPI Connect+ 32GB

Z9000032



Revolution Pi Connect+ based on Raspberry Pi Compute module 3+. Quad-Core with 1.2 GHz and 1 GB RAM and a 32 Gbyte eMMC Flash memory. Two Ethernet sockets, two USB sockets, one Micro-HDMI socket and a Micro-USB socket. As an operating system the device has an adapted version of Raspbian with RT-Patch, housing dimensions (H x W x D): 96 x 45 x 110.5 mm, protection type: IP 20.

Technical details

General data

Approval: CE

Technical data

Electrical data

Supply voltage (V): 12 - 24 V

Type of supply voltage U1: DC

Inputs

Number of digital inputs: 1, 1

Environmental data

Ambient temperature: -40 - 55 °C

Humidity rating: 93 % r. h. at 40 °C

Condensation permitted?: Not permitted

Mechanical data

Housing material: Plastic

Height dimension: 96 mm

Width dimension: 45 mm

Depth dimension: 110.5 mm

Net weight: 224 g

Gross weight: 230 g

Environment

WEEE klassifikation (08/2018):	6 small IT-/communic. device
Commercial data	
ECLASS version:	ECLASS-9.1
ETIM Version:	ETIM-7.0
ETIM Reference Group:	EG000024
ETIM Reference Feature:	EC001413

Optional accessories



Z9000016

GW Connector for Modular Gateways



Z9000018

RevPi Con MBus VHP ext. module 169 MHz



Z9000019

RevPi Con MBus ext. module 868 MHz



Z9000020

RevPi Con CAN extension module



Z9000021

Connector for CON Bridge Module