

PSSu E S 4AO U

312465



PSSu, electronic module, standard, analogue inputs and outputs, 4 outputs, voltage range 0 - 10 V, single-pole, referenced to earth, resolution 12Bit.

Technical details

General data

Approval:	CE, UKCA, cULus Listed
Application range:	Standard

Technical data

Electrical data

Permitted loads:	Resistive, Capacitive
------------------	-----------------------

Analogue outputs

Number of analogue outputs:	4
Type of analogue outputs:	Voltage
Signal range analog output:	0 .. 10 V
Resolution, analogue outputs:	12 Bit
Potential isolation outputs:	Yes
Pot. isolation analog outp./:	Yes







Environmental data

Climatic suitability to ...:	EN 60068-2-30, EN 60068-2-2, EN 60068-2-1, EN 60068-2-78, EN 60068-2-14
Ambient temperature standard:	EN 60068-2-14
Ambient temperature:	0 - 60 °C
Storage temperature standard:	EN 60068-2-1/-2
Climatic suitability standard:	EN 60068-2-30, EN 60068-2-78
Humidity rating:	93 % r. h. at 40 °C

Condensation permitted?:	Not permitted
Perm. operating height ASL:	2000 m
EMC to standard:	EN 61000-4-4, EN 61000-6-2, EN 61000-4-5, EN 61000-6-4, EN 61000-4-6, EN 61000-4-2, EN 61000-4-3
Vibration to standard:	EN 60068-2-6
Acc. shock to standard1:	15g
Clearance & creepage dist. to:	EN 60664-1
Overvoltage category:	II
Pollution degree clear.&creep.:	2
Protection type standard:	EN 60529
Mechanical data	
Housing material lower section:	PC
Housing material front plate:	PC
Housing material code:	PA
Terminal style:	plug-in
Height dimension:	76 mm
Width dimension:	12.6 mm
Depth dimension:	60.2 mm
Net weight:	35 g
Gross weight:	43 g
Name of coding element:	E
Colour of coding element:	Dark grey
Environment	
REACH compliance:	contains min. 1 SVHC-substance
WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
Harmonized System Code:	85389091
UNSPSC 25:	39122331
EAN-Code:	4046548018509

ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27242601
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000024
ETIM Reference Feature:	EC001596
Volume:	0.049 dm3

Obligatory accessories

	312621	PSSu BP-C 1/12 C
	312610	PSSu BP-C 1/8 S
	312620	PSSu BP-C 1/12 S
	312601	PSSu BP 1/8 C
	312600	PSSu BP 1/8 S
	312611	PSSu BP-C 1/8 C



312618

PSSu BP 1/12 S



312619

PSSu BP 1/12 C

Optional accessories



312900

PSSu A ET (10 pcs.)



312902

PSSu A EC



312967

PSSu A LA0.1 (10 x 108 pcs.)



312901

PSSu A ETM (2 pcs.)



312958

PSSu A LA0 (10 x 108 pcs.)



312949

PSSu A ET PE (10 pcs.)