

PSS u2 EF 4DO 2A

328133



PSS u2, electronic module, failsafe, 4 outputs, semiconductor 2 A, single-pole, switch-off delay, positive-switching, short circuit-proof, overload-proof, 1-row, terminalblock PSS u2 T 8 required (not supplied with the system).

Technical details

General data	
Approval:	CE, UKCA, cULus Listed, KOSHA, TÜV, EAC (Eurasian)
Application range:	Failsafe
Technical data	
Electrical data	
Permitted loads:	Resistive, Inductive, Capacitive
Semiconductor outputs	
Potential isolation S/C O:	Yes
S/C output short circuit proof:	Yes
Environmental data	
Climatic suitability to ...:	EN 60068-2-30, EN 60068-2-2, EN 60068-2-1, EN 60068-2-78, EN 60068-2-14
Ambient temperature standard:	EN 60068-2-14
Ambient temperature:	0 - 60 °C
Storage temperature standard:	EN 60068-2-1/-2
Climatic suitability standard:	EN 60068-2-78
Humidity rating:	93 % r. h. at 40 °C
Condensation permitted?:	Not permitted
Perm. operating height ASL:	2000 m
EMC to standard ...:	EN 61131-2 (Zone B)
Vibration to standard ...:	EN 60068-2-6

Acc. shock to standard1:	150 m/s ²
Clearance & creepage dist. to:	EN 61131-2, UL/IEC 61010-2-201
Overtoltage category:	II
Pollution degree clear.&creep.:	2
Protection type standard:	EN 60529
Potential separation	
Potential isolation 1 between:	SC output and module supply
Type of potential isolation 1:	Functional insulation
Potential isolation 2 between:	Periphery and module supply
Type of potential isolation 2:	Functional insulation
Mechanical data	
Housing material:	PC
Terminal style:	plug-in
Height dimension:	110.8 mm
Width dimension:	12.5 mm
Depth dimension:	72.5 mm
Net weight:	34 g
Gross weight:	43 g
Environment	
REACH compliance:	contains min. 1 SVHC-substance
WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
Harmonized System Code:	85389091
UNSPSC 25:	39122331
EAN-Code:	4046548072105
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27242604
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000024

ETIM Reference Feature:	EC001599
Volume:	0.216 dm ³

Obligatory accessories



328840

PSS u2 T 8 (1 pc.)

Optional accessories



328913

PSS u2 A LA E1 (10 pcs.)




328914

PSS u2 A LA E2 (10 pcs.)



328911

PSS u2 A LC E2 (10 pcs.)



328912

PSS u2 A LC T3 (10 pcs.)



328860

PSS u2 A CE E (10 pcs.)



328810

PSS u2 B 4

328910

PSS u2 A LC E1 (10 pcs.)



328811

PSS u2 B 1



328841

PSS u2 T 8 (10 pcs.)



328842

PSS u2 T 8 (5 x 10 pcs.)

