

PSS67 Supply Cable IN af, B, 10m

380261



Connection cable, PUR, black RAL9005, suitable for drag chains, 5-pin, socket angled M12, on open line end, B-coded, cable length: 10m

Technical details

General data	
Approval:	CE, UKCA, cULus Listed
Technical data	
Electrical data	
Rated current:	4 A
Specific contact resistance K1:	$\geq 1E+14 \text{ Ohm*cm}$
Specific conductor capacity K1:	105pF/m
Environmental data	
Ambient temperature:	-5 - 70 °C
Pollution degree clear.&creep.:	3
Mechanical data	
Connector type 1:	5-pin M12 female connector
Shape of connector type 1:	angled
Contact surfaces material 1:	Au
Material of sockets:	CuSn
Cable material K1:	Cu
Insulation material cable K1:	PVC
Cable type K1:	LiYY11Y
Length cable:	10 m
Colour cable insulation 1:	Black, similar to RAL9005

Housing colour:	Black
Material of cable insulation 1:	PUR
Trailing capability of cable 1:	no
Max. outside diameter cable K1:	5.9 - 5.9 mm
Conductor cross section:	0.5 - 0.5 mm ²
Cable cross section AWG K1:	20
Stranding K1:	5 cores round PP splice yarn
Shielding K1:	no
Number of conductors:	5
Approvals for connector 1:	UL94 V-0
Housing material:	PUR
Net weight:	541 g
Gross weight:	551 g
Environment	
WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
Harmonized System Code:	85444290
UNSPSC 25:	26121636
EAN-Code:	4046548054590
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27060411
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000037
ETIM Reference Feature:	EC002599
Volume:	2.188 dm ³