

SafetyNET p Connector RJ45s

380400

RJ45 plug-in connector, straight, IP20, 4-pin, Cat5e, AWG 22 (4-core), cable diameter: 6.3-6.7mm



Technical details

General data	
Approval:	-
Technical data	
Electrical data	
Rated current:	0.5 A
Environmental data	
Ambient temperature:	-40 - 70 °C
Mechanical data	
Connector type 1:	4-pin RJ45 male connector
Shape of connector type 1:	straight
Contact surfaces material 1:	Au
Material of pins:	Cu alloy
Material shield surface K1:	Ni
Category of cable K1:	Cat5e
Housing colour:	Signal yellow RAL1003
Max. outside diameter cable K1:	6.3 - 6.7 mm
Max. cable cross section K1:	0.75mm ²
Max. cable cross sect. AWG K1:	22
Net weight:	10 g
Gross weight:	60 g

Environment	
RoHS directive:	2011/65/EU, 2015/863/EU
RoHS conformity:	yes
RoHS exceptions:	no
REACH compliance:	Contains no SVHC substances
WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
Harmonized System Code:	85366990
UNSPSC 25:	26121603
EAN-Code:	4046548055726
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27440304
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000047
ETIM Reference Feature:	EC000516
Volume:	0 dm ³