

PDP67 cable M12-5sm, 3m

380705



Connection cable, PUR, yellow RAL1003, 5-pin, connector straight M12, on open line end, A-coded, cable length: 3m

Technical details

General data

Approval: CE, UKCA, cULus Listed

Technical data

Electrical data

| | |
|---------------------------------|---------------------|
| Rated current: | 4 A |
| Typ. conductor resistance K1: | 79 Ohm/km |
| Specific contact resistance K1: | $\geq 7E+15$ Ohm*cm |
| Specific conductor capacity K1: | 64.6pF/m |

Environmental data

| | |
|---------------------------------|-------------|
| Ambient temperature: | -25 - 80 °C |
| Pollution degree clear.&creep.: | 3 |

Mechanical data

| | |
|-------------------------------|--------------------------|
| Connector type 1: | 5-pin M12 male connector |
| Shape of connector type 1: | straight |
| Coding of M12 connector 1: | A coded |
| Contact surfaces material 1: | Au |
| Material of pins: | CuZn |
| Cable material K1: | Cu |
| Insulation material cable K1: | PP (9Y) |
| Cable type K1: | LiF9Y11Y |

| | |
|---------------------------------|------------------------------|
| Length cable: | 3 m |
| Colour cable insulation 1: | Yellow, similar to RAL 1003 |
| Housing colour: | Black |
| Material of cable insulation 1: | TPU / TPE-U, PUR |
| Trailing capability of cable 1: | yes |
| Bend radius (when laying) K1: | 5 x Ø |
| Max. outside diameter cable K1: | 5.1 - 5.1 mm |
| Conductor cross section: | 0.25 - 0.25 mm ² |
| Cable cross section AWG K1: | 24 |
| Stranding K1: | 5 cores round filler |
| Shielding K1: | no |
| Number of conductors: | 5 |
| Approvals for cable K1: | UL AWM-Style 20233, UL/CSA |
| Approvals for connector 1: | UL94 V-0 |
| Halogen-free: | yes |
| Oil resistance: | resistant |
| Flame resistance: | UL VW1 |
| Housing material: | PUR |
| Net weight: | 125 g |
| Gross weight: | 130 g |
| Environment | |
| RoHS directive: | 2011/65/EU, 2015/863/EU |
| RoHS conformity: | yes |
| RoHS exceptions: | no |
| REACH compliance: | Contains no SVHC substances |
| WEEE classification (08/2018): | 5 devices (feed size < 50cm) |
| Commercial data | |
| Harmonized System Code: | 85444290 |
| UNSPSC 25: | 26121603 |

| | |
|---------------------------|---------------|
| EAN-Code: | 4046548065633 |
| ECLASS version: | ECLASS-13 |
| ECLASS Reference Feature: | 27060311 |
| ETIM Version: | ETIM-9.0 |
| ETIM Reference Group: | EG000026 |
| ETIM Reference Feature: | EC001855 |
| Volume: | 0.512 dm3 |