



PITestop active, set consisting of E-STOP pushbutton can be activated/deactivated with flashing function, without logo and without E-STOP symbol, with contact block with dropout protection in accordance with EN 60947-5-1 and EN 60947-5-5 and with LED safety module PCB in the surface mount housing with M12/5-pin connection - PDP67 8DI ION PIN assignment, 2 N/C (2 N/C) in quick-connection technology.

Technical details

General data	
Approval:	CE, UKCA, TÜV
Self-monitored:	yes
Lamp:	LED
Lamp colour:	yellow, red
Technical data	
Electrical data	
Rated operating voltage:	24 V DC
Emergency stop	
Release type emergency stop:	Turn release
Switch cap. E-STOP to standard:	EN 60947-5-1
Contact fuse protection E-Stop:	≤ 1 A
Contact material E-STOP:	AgNi
Environmental data	
Ambient temperature:	-25 - 55 °C
Vibration to standard ...:	EN 60947-5-5
Peak amplitude:	Max. 0.35 mm
Clearance & creepage dist. to:	EN 60947-5-1
Overvoltage category:	II
Pollution degree clear.&creep.:	2

Mechanical data	
Mounting position:	any
Connection terminal:	M12
Height dimension:	124.5 mm
Width dimension:	72.1 mm
Depth dimension:	86 mm
Net weight:	295 g
Gross weight:	305 g
Environment	
WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27371244
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000017
ETIM Reference Feature:	EC002034
UNSPSC 25:	46171620
GTIN:	4046548085877
Volume:	0.829 dm ³
Harmonized System Code:	85365011
Type of tariff number:	TARIC
Use of customs tariff number:	Ausfuhr, Einfuhr
Quantity per packaging unit:	1

Optional accessories



400220

PIT es box flex bracket