

## PSEN im1

535130



Interfaces PSEN im1 for connecting and evaluating several pressure-sensitive safety mats to the PNOZmulti system, 96 x 48 x 43.5mm (H x W x D), connection type spring-loaded terminals.

## Technical details

### General data

Approval: CE, UKCA, cULus Listed

### Technical data

### Electrical data

Type of supply voltage U1: DC

### Environmental data

Climatic suitability to ...: DIN IEC 60068-2-3

Ambient temperature: 0 - 60 °C

EMC to standard ...: EN 60947-5-3

Vibration to standard ...: EN 60068-2-6

Clearance & creepage dist. to: VDE 0110-1

Protection type standard: EN 60529

### Mechanical data

Connection terminal: Spring-loaded terminal

Height dimension: 96 mm

Width dimension: 48 mm

Depth dimension: 43.5 mm

Net weight: 83 g

Gross weight: 93 g

### Environment

WEEE klassifikation (08/2018):	5 devices (feed size < 50cm)
Commercial data	
Harmonized System Code:	85389091
UNSPSC 25:	39122205
EAN-Code:	4046548026795
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27440108
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000026
ETIM Reference Feature:	EC002585
Volume:	0.263 dm <sup>3</sup>