

## PSEN/PDP67 M12-8sf screw terminals

540332



Plug-in connector, 8-pin, socket straight M12, A-coded, screwconnection, material threaded ring: Zinc die casting nickel-plated, outer cable diameter 6- 8mm

## Technical details

### General data

### Technical data

### Electrical data

Rated current: 2 A

### Environmental data

Ambient temperature: -40 - 85 °C

Pollution degree clear.&creep.: 3

### Mechanical data

Connector type 1: 8-pin M12 female connector

Shape of connector type 1: straight

Coding of M12 connector 1: A coded

Contact surfaces material 1: Au

Material of sockets: CuSn

Housing colour: Black

Max. cable cross section K1: 0.75mm<sup>2</sup>

Max. cable cross sect. AWG K1: 18

Approvals for connector 1: UL 94 HB

Net weight: 26 g

Gross weight: 28 g

### Environment

WEEE klassifikation (08/2018):	5 devices (feed size < 50cm)
Commercial data	
Harmonized System Code:	85369010
UNSPSC 25:	39122205
EAN-Code:	4046548065404
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27272492
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000026
ETIM Reference Feature:	EC002594
Volume:	0 dm3