

PSEN cs3.1p Key 1 switch

541065



Safety switch for transponder key PSEN cs4.1 Key, 2 safety outputs, M8, 8-pin male connector, coded, accessories: key adapter (532113) and key (541181 or 541182 or 541183 or 541184)

Technical details

General data

Approval:	CE, UKCA, cULus Listed, FCC, IC, EAC (Eurasian), TÜV
Sensor principle:	Transponder
Coding level to ISO 14119:	Low
Classification to EN 60947-5-3:	PDDB
Transponder coding:	coded
Suitable for series connection:	yes
unit type:	Sensor

Technical data

Electrical data

Supply voltage (V):	24 - 24 V
Type of supply voltage U1:	DC
Power consumption DC:	1 W

Inputs

Number of inputs:	2
DC voltage at input:	24 V DC

Semiconductor outputs

Number of OSSD outputs:	2
Number of sig. outputs:	1
Potential isolation S/C O:	No

S/C output short circuit proof:	Yes
Utilisation cat. to EN 60947-1:	DC-12
Environmental data	
Ambient temperature standard:	EN 60068-2-14
Ambient temperature:	-10 - 55 °C
Max. ambient temp. at 2000 m:	+55 °C
Storage temperature standard:	EN 60068-2-1/-2
Climatic suitability standard:	EN 60068-2-78
Humidity rating:	93 % r. h. at 40 °C
Perm. operating height ASL:	4000 m
EMC to standard ...:	EN 60947-5-3
Vibration to standard ...:	EN 60947-5-2
Acc. shock to standard1:	30g
Overvoltage category:	III
Pollution degree clear.&creep.:	3
Mechanical data	
Bend radius (when laying) K1:	5 x Ø
Sensor can be flush-mounted:	Yes, follow installation guide
Connection type:	M8, 8-pin male
Cable lines:	Li9Y11Y 8 x 0.14 mm ²
Housing material upper part:	PBT
Height dimension:	37 mm
Width dimension:	26 mm
Depth dimension:	18 mm
Net weight:	35 g
Gross weight:	50 g
Transponder	
Operating frequency:	122 kHz - 128 kHz
Environment	

WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27274601
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000026
ETIM Reference Feature:	EC002592
UNSPSC 25:	39122205
GTIN:	4046548099805
Volume:	0 dm3
Harmonized System Code:	85365019
Type of tariff number:	TARIC
Use of customs tariff number:	Ausfuhr, Einfuhr
Quantity per packaging unit:	1

Obligatory accessories



541186

PSEN cs4.1 Key bl



541181

PSEN cs4.1 Key gy1



541182

PSEN cs4.1 Key gy2



541183

PSEN cs4.1 Key gy3



541184

PSEN cs4.1 Key gy4

Optional accessories



533150

PSEN cable M8-8sf, 2m



540337

PSEN Y junction M8-M12/M12 PIGTAIL



540342

PSEN cable M12-8sf M12-8sm, 10m



540343

PSEN cable M12-8sf M12-8sm, 20m



540344

PSEN cable M12-8sf M12-8sm, 30m



533157

PSEN cable M8-8sf M8-8sm, 2m



533156

PSEN cable M8-8sf M8-8sm, 1m



533155

PSEN cable M8-8sf M8-sm, 0.5m



532110

PSEN Winkel / bracket



533154

PSEN cable M8-8sf, 30m



540329

PSEN converter M8-8sf -- M12-8sm



533153

PSEN cable M8-8sf, 20m



533152

PSEN cable M8-8sf, 10m



533151

PSEN cable M8-8sf, 5m



532114

PSEN cs key adapter bracket



540130

SDD ES ETH



540340

PSEN cable M12-8sf M12-8sm, 2m



540341

PSEN cable M12-8sf M12-8sm, 5m



773603

PDP67 F 4 code
