



Transponder key for PSEN cs4.1p, grey "1" marking, material: plastic, accessories: key adapter (532113)

Technical details

General data	
Approval:	CE, UKCA, cULus Listed, FCC, IC, TÜV, EAC (Eurasian)
Sensor principle:	Transponder
Coding level to ISO 14119:	High
Transponder coding:	fully coded
unit type:	Actuator
Technical data	
Environmental data	
Ambient temperature standard:	EN 60068-2-14
Ambient temperature:	-10 - 55 °C
Max. ambient temp. at 2000 m:	+55 °C
Storage temperature standard:	EN 60068-2-1/-2
Climatic suitability standard:	EN 60068-2-78
Humidity rating:	93 % r. h. at 40 °C
Perm. operating height ASL:	4000 m
EMC to standard:	EN 60947-5-3
Vibration to standard:	EN 60947-5-2
Acc. shock to standard1:	30g
Mechanical data	
Housing material upper part:	PBT

Height dimension:	15.1 mm
Width dimension:	42 mm
Depth dimension:	8 mm
Net weight:	5 g
Gross weight:	6 g
Transponder	
Operating frequency:	122 kHz - 128 kHz
Environment	
WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27274692
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000026
ETIM Reference Feature:	EC002997
UNSPSC 25:	39122205
GTIN:	4046548096668
Volume:	0 dm ³
Harmonized System Code:	85389099
Type of tariff number:	TARIC
Use of customs tariff number:	Ausfuhr, Einfuhr
Quantity per packaging unit:	1