

PSEN me1.02S/AR M12

570012



Mechanical safety guard locking device, with radius actuator, interlock principle spring force, contacts: 2 N/O, 2 N/C, supply voltage 24 V AC/DC, M12/8-pin connection.

Technical details

General data

Approval:	CE, BG, cCSAus, EAC (Eurasian)
unit type:	Unit

Technical data

Electrical data

Supply voltage (V):	24 - 24 V
Type of supply voltage U1:	AC/DC

Relay outputs

Utilisation cat. AC15/DC13sta.:	EN 60947-5-1
---------------------------------	--------------

Environmental data

Mechanical data

Holding force:	1500 N
Connection type:	M12, 8-pin
Height dimension:	204.5 mm
Width dimension:	42.5 mm
Depth dimension:	51 mm
Net weight:	348 g
Gross weight:	440 g

Environment

RoHS directive:	2011/65/EU, 2015/863/EU
-----------------	-------------------------

RoHS conformity:	yes
RoHS exceptions:	yes
RoHS except.s acc. to direct.:	6c
REACH compliance:	contains min. 1 SVHC-substance
REACH included substances:	Lead, Butylphenol
%-part of the pollutant:	> 0,1
CAS No.:	7439-92-1, 98-54-4
SCIP entry available:	yes
WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27272603
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000026
ETIM Reference Feature:	EC002593
UNSPSC 25:	39122205
GTIN:	4046548094787
Volume:	1.330 dm3
Harmonized System Code:	85365080
Type of tariff number:	TARIC
Use of customs tariff number:	Ausfuhr, Einfuhr
Quantity per packaging unit:	1

Optional accessories



540346

PSEN cable M12-8sf M12-8sm, 1m



540324

PSEN cable angle M12 8-pole 10m



540347

PSEN cable M12-8sf M12-8sm, 1,5m



540325

PSEN cable angle M12 8-pole 30m



540326

PSEN cable axial M12 8-pole 30m



380704

PDP67 cable M12-8sm, 30m



540342

PSEN cable M12-8sf M12-8sm, 10m



540320

PSEN cable axial M12 8-pole 5m












540343


PSEN cable M12-8sf M12-8sm, 20m




540321

PSEN cable axial M12 8-pole 10m

	540344	PSEN cable M12-8sf M12-8sm, 30m
	540322	PSEN cable angle M12 8-pole 3m
	540345	PSEN cable M12-8sf M12-8sm, 0,5m
	540323	PSEN cable angle M12 8-pole 5m
	630368	PSEN op cable axial M12 8-p. shield. 50m
	630369	PSEN op cable angle M12 8-p. shield. 50m
	630328	PSEN op cable axial M12 8-p. shield. 30m
	570793	PSEN cable 200m-8x0.25mm ²
	630329	PSEN op cable angle M12 8-p. shield. 30m

	380702	PDP67 cable M12-8sm, 10m
	380703	PDP67 cable M12-8sm, 20m
	380700	PDP67 cable M12-8sm, 2m
	380701	PDP67 cable M12-8sm, 5m
	540332	PSEN/PDP67 M12-8sf screw terminals
	540333	PSEN cable M12-8sf, 20m
	540334	PSEN/PDP67 M12-8sm screw terminals
	630313	PSEN op cable axial M12 8-p. shield. 3m
	630314	PSEN op cable axial M12 8-p. shield. 5m

	630317	PSEN op cable angle M12 8-p. shield. 5m
	630318	PSEN op cable angle M12 8-p. shield. 10m
	540319	PSEN cable axial M12 8-pole 3m
	630315	PSEN op cable axial M12 8-p. shield. 10m
	630316	PSEN op cable angle M12 8-p. shield. 3m
	540340	PSEN cable M12-8sf M12-8sm, 2m
	540341	PSEN cable M12-8sf M12-8sm, 5m