

PSEN me1.02S / AA

570017



Mechanical safety switch with angle actuator Interlock principle spring force
Contacts 2 N/O, 2 N/C Supply voltage 24 V AC/DC.

Technical details

General data	
Approval:	CE, cCSAus
unit type:	Unit
Technical data	
Electrical data	
Supply voltage (V):	24 - 24 V
Type of supply voltage U1:	AC/DC
Relay outputs	
Utilisation cat. AC15/DC13sta.:	EN 60947-5-1
Environmental data	
Mechanical data	
Holding force:	1500 N
Height dimension:	204.5 mm
Width dimension:	42.5 mm
Depth dimension:	51 mm
Net weight:	358 g
Gross weight:	450 g
Environment	
RoHS directive:	2011/65/EU, 2015/863/EU
RoHS conformity:	yes

RoHS exceptions:	yes
RoHS except.s acc. to direct.:	6c
REACH compliance:	contains min. 1 SVHC-substance
REACH included substances:	Lead
%-part of the pollutant:	> 0,1
CAS No.:	7439-92-1
SCIP entry available:	yes
WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27272603
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000026
ETIM Reference Feature:	EC002593
UNSPSC 25:	39122205
GTIN:	4046548099713
Volume:	1.330 dm ³
Harmonized System Code:	85365080
Type of tariff number:	TARIC
Use of customs tariff number:	Ausfuhr, Einfuhr
Quantity per packaging unit:	1

Optional accessories



570793

PSEN cable 200m-8x0.25mm²