



Mechanical safety switch, with radius actuator, contacts: 1 N/C.

Technical details

General data	
Approval:	CE, cCSAus, TÜV, EAC (Eurasian)
unit type:	Unit
Technical data	
Relay outputs	
Utilisation cat. AC/DC1 stand.:	EN 60947-4-1
Voltage AC1 safety cont.:	240 V
Max. current AC1 safety cont.:	5 A
Utilisation cat. AC15/DC13sta.:	EN 60947-5-1
Voltage AC15 safety cont.:	240 V
Max. current AC15 safety cont.:	1.5 A
Environmental data	
Ambient temperature:	-30 - 80 °C
Mechanical data	
Connection terminal:	Screw terminal
Terminal style:	fixed
Height dimension:	75 mm
Width dimension:	52 mm
Depth dimension:	33 mm
Net weight:	146 g









Gross weight:	209 g
Environment	
RoHS directive:	2011/65/EU, 2015/863/EU
RoHS conformity:	no
RoHS exceptions:	yes
RoHS except.s acc. to direct.:	6a, 6c
REACH compliance:	contains min. 1 SVHC-substance
REACH included substances:	Lead, ETU
%-part of the pollutant:	> 0,1
CAS No.:	7439-92-1, 96-45-7
WEEE classification (08/2018):	5 devices (feed size < 50cm)
SCIP entry available:	0
Commercial data	
Harmonized System Code:	85365080
UNSPSC 25:	39122205
EAN-Code:	4046548002829
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27272603
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000026
ETIM Reference Feature:	EC002593
Volume:	0 dm ³

Optional accessories



380706

PDP67 cable M12-5sm, 10m

	380707	PDP67 cable M12-5sm, 20m
	380705	PDP67 cable M12-5sm, 3m
	570206	PSEN me2AR
	380708	PDP67 cable M12-5sm, 30m
	540312	PSEN screw M5x20 10pcs
	570205	PSEN me2AS
	773600	PDP67 F 8DI ION
	570793	PSEN cable 200m-8x0.25mm ²