

PSEN rs1.0-300

570300



Rope pull switch incl. E-STOP pushbutton, metal housing, 2xNC+2xNO contacts, 300 N max. spring force.

Technical details

General data

Approval: CE, BG, cCSAus

Technical data

Relay outputs

Utilisation cat. AC15/DC13sta.: EN 60947-5-1

Voltage AC15 safety cont.: 240 V

Max. current AC15 safety cont.: 3 A

Voltage DC13 safety cont.: 250 V

Environmental data

Ambient temperature: -30 - 80 °C

Mechanical data

Housing material lower section: Aluminium die cast

Housing material upper part: Aluminium die cast

Material actuator: Zn die cast

Connection terminal: Screw terminal

Height dimension: 88 mm

Width dimension: 282 mm

Depth dimension: 90.1 mm

Net weight: 939 g

Gross weight: 1056 g

Environment	
RoHS directive:	2011/65/EU, 2015/863/EU
RoHS conformity:	yes
RoHS exceptions:	yes
RoHS except.s acc. to direct.:	6b, 6c
REACH compliance:	contains min. 1 SVHC-substance
REACH included substances:	Lead
%-part of the pollutant:	> 0,1
CAS No.:	7439-92-1
WEEE classification (08/2018):	5 devices (feed size < 50cm)
SCIP entry available:	yes
Commercial data	
Harmonized System Code:	85365080
UNSPSC 25:	39122205
EAN-Code:	4046548062816
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27270607
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000017
ETIM Reference Feature:	EC002033
Volume:	0

Optional accessories



380706

PDP67 cable M12-5sm, 10m



380707

PDP67 cable M12-5sm, 20m



380705

PDP67 cable M12-5sm, 3m



570314

PSEN rs rope d3/d4 50m



380708

PDP67 cable M12-5sm, 30m



570315

PSEN rs rope d3/d4 100m



570312

PSEN rs pulley 75



570313

PSEN rs pulley flex



570310

PSEN rs spring 175



773600

PDP67 F 8DI ION



570311

PSEN rs spring 300



570793

PSEN cable 200m-8x0.25mm²
