

PSEN rs spring 300

570311



Rope pull spring for max. 300 N spring force.

Technical details

Technical data

Environmental data

Ambient temperature: -25 - 70 °C

Mechanical data

Height dimension: 50 mm

Width dimension: 300 mm

Depth dimension: 90 mm

Net weight: 576 g

Gross weight: 638 g

Environment

RoHS directive: 2011/65/EU, 2015/863/EU

RoHS conformity: yes

RoHS exceptions: yes

RoHS except.s acc. to direct.: 6a

REACH compliance: contains min. 1 SVHC-substance

REACH included substances: Lead

%-part of the pollutant: > 0,1

CAS No.: 7439-92-1

WEEE classification (08/2018): 0 not relevant

SCIP entry available: 0

Commercial data	
Harmonized System Code:	73202081
UNSPSC 25:	39122205
EAN-Code:	4046548062847
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27272691
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000017
ETIM Reference Feature:	EC002026
Volume:	0 dm3